

Filling Machine Tooling & Applications

Accessories supplied with ALL-FILL

Filling Machines are used for products

with different filling characteristics for

the most efficient use of the machine.

The following lists typical applications

of filling accessories available for

auger fillers. The mechanical


configuration of accessories installed

on an auger filler for different types of


products is presented on this page.

Filling Accessory Applications


PRODUCT	EXAMPLES	ACCESSORIES
Non-Freeflowing Powders	Bakery Mixes, Carbon, Talcum Powder, etc.	Slow Speed Agitator, High Speed Agitator (Type D), Self-Feeding Auger, Lip Funnel. For products that drip slightly at the end of fill, Drip Washer can be used.
Freeflowing Products	Granulated sugar, salt, bread crumbs, etc.	Straight Auger, High Speed Agitator (A-3), Slow Speed Agitator or Flake Blade, Straight Funnel, Collector Funnel Cover, Spinner Plate, Dividing Head (2 or more containers per fill for borderline products), Type D High Speed Agitator, Lip Funnel.
Liquids and Pastes	Creams, Shampoo, Oils, Gels, etc.	Rotor, Stator, and Pump Housings (1-4), Dispensing Nozzle, Cutoffs.



Freeflowing



Liquids and Pastes



Non-Freeflowing



Accessories used with a particular filling machine will depend on a variety of factors, including: Product Flow Characteristics and Density, Filled Amounts, Container Size & Configuration, Filling Times, and Accuracy. Before making the final selection and setup of accessories, the product and container should be tested to ensure that the machine will fulfill your requirements. ALL-FILL offers thorough testing services and facilities for the analysis of products and suitability of accessories.